Choose your Clearfield® Hybrid

There are 7 Clearfield® hybrids available for Autumn 2023. All of them are tolerant to ALS herbicide residues which may be present in the soil, giving them the quickest start possible. Make sure to discuss the varieties with your agronomist or seed seller, so you can decide which best suits your needs.

Variety	Recommended List 2022	Breeder	
InV1266 CL		BASF	
PT 279 CL	E/W Sp	Corteva	
PX 125 CL			
DK Imprint CL	UK Sp	Dekalb	
Matrix CL	UK Sp	- DSV	
Beatrix CL	N Sp		
LG Constructor CL	UK Sp	Limagrain	

E/W

= Recommended for

N = Recommended for the North Rea

= Specific recommendation

Please visit seed breeders website for full details




Apply Cleravo® herbicide

To get the best weed control, treat Clearfield® hybrids with Cleravo®. Specifically formulated to work in tandem with Clearfield® varieties, and offering the widest range of broadleaved weed control, Cleravo® even controls brassica weeds such as charlock, runch, and hedge mustard. Cleravo® is crop kind, even at early application timings and can be applied from expanded cotyledon.

Crop	Clearfield WOSR (& SOSR) hybrids only
Recommendation	Cleravo 1.0l/ha + Dash HC 1.0l/ha
Max applications	One
Crop timing	From expanded cotyledon to <8 true leaves (GS 19)
Soil type	Light, medium, heavy
Aquatic buffer zone	
Pack size	5 litres

02

Apply Cleravo® herbicide





Smart Stewardship

wHen2g0 is a smart tool which helps with application timings of quinmerac to minimise risk to water. By evaluating a combination of soil type, drainage, cultivation method and weather, the tool provides an eight day forecast with a traffic light system, indicating the optimum timing for water stewardship.

wHen2g0 should be checked in advance of a Cleravo® application to ensure you follow the best water stewardship advice. Scan the QR code to try it for yourself.




Cleravo® contains imazamox and quinmerac Cleravo® is a registered Trademark of BASF. © BASF 2022. All rights reserved.





Choose your Clearfield® Hybrid



dentsu MCGARRYBOWEN.

MASTER	BBASF0056_BASF_CLEARFIELD_GATFOLD_A5_MASTER		Operator: CH	BBASF0056
Date: 27/04/22	Mech size: 210x148.5mm	Mech built at 1:1 of final output size	CMYK	DDASFUUSU